


# **LENSER KF CGR**

CHAMBER FILTER ELEMENT – STANDARD, SEALED



FOR FILTER CHAMBERS THAT MUST BE ABSOLUTELY DRIP-TIGHT

EQUIPPED WITH CLOTH TENSIONING GROOVE AND O-RING SEALING

#### LENSER KF CGR

LENSER KF CGR are used when the filter chambers must be absolutely drip-tight.

Depending on the resistance requirements, LENSER offers a variety of sealing materials such as EPDM, silicone, NBR and FKM. For the food and pharmaceutical sector, we use FDA or EU-compliant seals, among others.

## **FEATURES**

- For filter chambers that must be absolutely drip-tight
- Different sealing materials available according to requirements
- Compatible with critical chemical conditions through the use of additives

#### **BENEFITS**

- Available in PVDF for chemically harsh conditions
- FDA-compliant, antistatic or ATEX-compliant on request
- Equipped with cloth clamping groove (Ω-type or U-type) and O-ring sealing

#### Feed port position









Version



С

### **TECHNICAL DATA**

off-centre

Size	From 470 mm to 2.500 mm
Cake thickness	From 25 mm to 35 mm
Filtration pressure	Up to 8 bar
Feed port position	Centre, off-centre, corner, external
Version	С



**LENSER Filtration GmbH**Breslauer Strasse 8
89250 Senden
Germany

p. +49 7307 / 801-0 info@lenser.de lenser.de/en



